



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB1050 Type Bab Circuit BRKR 1P, 50AMP 40C 120/240V 10, 000**

*Eaton Corp*

Catalog Number	BAB1050
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 50 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.8000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

### **Descriptions**

Description	TYPE BAB CIRCUIT BRKR 1P,50AMP 40C 120/240V 10,000
extra long description	ETN BAB1050 BAB, 1p, 50A, 120/240V,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,50 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab, 1P, 50A, 120/240V, 10kaic
Special Features	High intensity discharge

### **Manufacturer Information**

Brand	Eaton Corp
GTIN	00786679301500
Manufacturers Part Number	BAB1050
UPC	786679301500

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### **Packaging**

Carton	1
Weight Per each	0.35



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative  
EnergyOtherGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other

standard

UL Listed,CSA Certified