



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2070 BRKR 2 Pole 70a

Eaton Corp

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | BAB2070 |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, 70 A, 3 Kaic, Two-Pole, 240/415 V, Non-Interchangeable, Q7, Bab |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | 2 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.6000 IN X 2.2000 IN X 3.7000 IN |
| interrupt rating | 10 |
| Poles | 2 |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | BRKR 2 POLE 70A |
| extra long description | ETN BAB2070 BAB BREAKER 2P 70A MAX |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, 70 A, 3 kAIC, Two-pole, 240/415 V, Non-Interchangeable, Q7, BAB |
| Product Type | Bab Breaker 2P 70A Max 240V Max 10K Aic |
| Special Features | Bolt-on mounting |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton Corp |
| GTIN | 00786679302705 |
| Manufacturers Part Number | BAB2070 |
| UPC | 786679302705 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 1.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional
EnergyGeneration - Renewable Energy - Alternative
EnergyOtherMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherDatacenters - IT Space: CI and Hyper
ConvergedResidential Bldgs & Facilities - Residential Bldgs &
Facilities - Other

standard

CSA Certified,UL Listed