



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB3080H Bab 3 Pole 80A BRKR**

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | BAB3080H  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 80A, Bab Type, 10 Kaic, Bolt-On Mounting, Three-Pole, Non-Interchangeable, 240V |
| Weight per unit  | 1.0 (lbs/each)  |
| Product Category | 3 Pole Standard Trip Bolt-On  |

### **Features**

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 3.8000 IN X 3.2000 IN X 4.7000 IN |
| interrupt rating | 10                                |
| media            | Yes                               |
| Poles            | 3                                 |
| Voltage Rating   | 240 V - 240 V                     |

### **Descriptions**

|                        |  |
|------------------------|--|
| Description            | BAB 3 POLE 80A BRKR  |
| extra long description | ETN BAB3080H 80A, 3 pole circuit br  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 80A, BAB type, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V  |
| Product Type           | 80A, 3 Pole Circuit Breaker, Pow-R-Line  |
| Special Features       | Bolt-on mounting   |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton Corp     |
| GTIN                      | 00786679303801 |
| Manufacturers Part Number | BAB3080H       |
| UPC                       | 786679303801   |

### **Taxonomies, Classifications, and Categories**

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |

### **Packaging**

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Package         | 8 |
| Weight Per each | 1 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional  
EnergyGeneration - Renewable Energy - Alternative  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other

standard

UL Listed,CSA Certified