



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB1015 Type Bab BRKR 120/240 Vac Max 1 Pole 15A 10kaic**

*Eaton Corp*

Catalog Number	BAB1015
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 15 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab, Ring or Spade Lug Terminals
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.7000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

### **Descriptions**

Description	TYPE BAB BRKR 120/240 VAC MAX 1 POLE 15A 10KAIC
extra long description	ETN BAB1015 BAB, 1p, 15A, 120/240V,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,15 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB, Ring or spade lug terminals
Product Type	Bab, 1P, 15A, 120/240V, 10kaic
Special Features	High intensity discharge

### **Manufacturer Information**

Brand	Eaton Corp
GTIN	00786679301159
Manufacturers Part Number	BAB1015
UPC	786679301159

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	24
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed