

## Cable To Wire and Rod Fasteners

- Supports cable from #12 wire thru  $\frac{3}{8}$ " threaded rod.
- Cable retainer clips are included with hooks.
- W2 series attaches to #12 wire thru  $\frac{1}{4}$ " plain or threaded rod.
- W6 series attaches to  $\frac{3}{8}$ " plain or threaded rod.
- Static Load Capacity: 25 Lbs.
- Finish: Pre-Galvanized.


Communication & Low Voltage



| UPC/Part Number | Catalog Number  | Description       | Box Qty. |
|-----------------|-----------------|-------------------|----------|
| 78205146573     | <b>BCH12-W2</b> | $\frac{3}{4}$ "   | 50       |
| 78101104819     | <b>BCH21-W2</b> | $1\frac{5}{16}$ " | 50       |
| 78101104841     | <b>BCH32-W2</b> | 2"                | 50       |
| 78205128082     | <b>BCH12-W6</b> | $\frac{3}{4}$ "   | 50       |
| 78101195567     | <b>BCH21-W6</b> | $1\frac{5}{16}$ " | 50       |
| 78101195569     | <b>BCH32-W6</b> | 2"                | 50       |

(See pages 235-236 for technical data.)

Read safety/installation instruction sheets in packages before use.



## Cable To T-Bar Fasteners


- Supports cable above ceiling grid and allows 360° rotation.
- Provides compliance with the EIA/TIA requirements.
- Permits dropwire attachment if required.
- Cable retainer clips are included with hooks.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-Galvanized.



| UPC/Part Number | Catalog Number   | Description | Box Qty. |
|-----------------|------------------|-------------|----------|
| 78205128083     | <b>BCH12-A28</b> | 3/4"        | 50       |
| 78101104857     | <b>BCH21-A28</b> | 15/16"      | 50       |
| 78101104858     | <b>BCH32-A28</b> | 2"          | 50       |

(See pages 235-236 for technical data.)

Read safety/installation instruction sheets in packages before use.



## Cable To Wire and Rod Fasteners

- Supports cable from #12 wire thru 3/8" threaded rod.
- Cable retainer clips are included with hooks.
- W2 series attaches to #12 wire thru 1/4" plain or threaded rod.
- W6 series attaches to 3/8" plain or threaded rod.
- Static Load Capacity: 25 Lbs.
- Finish: Pre-Galvanized.


Communication & Low Voltage



| UPC/Part Number | Catalog Number  | Description                      | Box Qty. |
|-----------------|-----------------|----------------------------------|----------|
| 78205146573     | <b>BCH12-W2</b> | 3/4"                             | 50       |
| 78101104819     | <b>BCH21-W2</b> | 1 <sup>5</sup> / <sub>16</sub> " | 50       |
| 78101104841     | <b>BCH32-W2</b> | 2"                               | 50       |
| 78205128082     | <b>BCH12-W6</b> | 3/4"                             | 50       |
| 78101195567     | <b>BCH21-W6</b> | 1 <sup>5</sup> / <sub>16</sub> " | 50       |
| 78101195569     | <b>BCH32-W6</b> | 2"                               | 50       |

(See pages 235-236 for technical data.)

*Read safety/installation instruction sheets in packages before use.*



## Cable To T-Bar Fasteners

- Supports cable above ceiling grid and allows 360° rotation.
- Provides compliance with the EIA/TIA requirements.
- Permits dropwire attachment if required.
- Cable retainer clips are included with hooks.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-Galvanized.



| UPC/Part Number | Catalog Number   | Description | Box Qty. |
|-----------------|------------------|-------------|----------|
| 78205128083     | <b>BCH12-A28</b> | 3/4"        | 50       |
| 78101104857     | <b>BCH21-A28</b> | 15/16"      | 50       |
| 78101104858     | <b>BCH32-A28</b> | 2"          | 50       |

(See pages 235-236 for technical data.)

Read safety/installation instruction sheets in packages before use.