



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BAB2040H BAB2040H BRKR A

Eaton Corp

Catalog Number	BAB2040H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 40 A, 10 Kaic, Two-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase
Weight per unit	9.0 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### Features

dimensions	3.0000 IN X 2.0000 IN X 3.5000 IN
interrupt rating	10
media	Yes
Poles	2
Voltage Rating	240 V - 240 V

### Descriptions

Description	BAB2040H BRKR A
extra long description	ETN BAB2040H TYPE BAB 40A 2P 240VAC
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 40 A, 10 kAIC, Two-pole, 240 V, Interchangeable, BAB, Distribution panels 240V (Three-phase, four-wire maximum), Four-wire, Three-phase
Product Type	Type Bab 40A 2P 240VAC Instant SWBD CB
Special Features	Bolt-on mounting

### Manufacturer Information

Brand	Eaton
GTIN	00786679302422
Manufacturers Part Number	BAB2040H
UPC	786679302422

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	9

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Datacenters - IT Space: CI and Hyper Converged Other Generation - Conventional Energy - Conventional Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed, CSA Certified