



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell  
88101-0000, NM Clovis  
Phone: 575-742-2504  
Fax: 575-742-2508



## BG16F13 SPRG 1" CNDT HNGR

*Cooper B-Line/Cable Tray*

Catalog Number	BG16F13
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Conduit Support Fasteners, Hangers, 1" Height, 1" Length, 1" Width, 0.065LBS, Conduit Size: 1", Guide-Rite Fastener, 100 LBS Load Capacity
Weight per unit	0.0700 (lbs/each)
Product Category	Anchors & Fasteners

### Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
Material	Cold Rolled High Carbon Steel

### Material, Color, and Finish

Color	Miscellaneous
Finish	Zinc Phosphate

### Dimensions and Weight

Size	1 In Conduit
------	--------------

### Descriptions

Description	SPRG 1" CNDT HNGR
extra long description	B-LINE BG-16-F13 "Z" PURL" HANGER,
Features	Designed for ease of installation, long service life and reliable performance, Eaton B-Line series conduit support fasteners provide the ideal choice for a wide range of applications.
Long Description	Eaton B-Line series conduit support fasteners, Hangers, 1" Height, 1" Length, 1" Width, 0.065lbs, Conduit size: 1", Guide-Rite fastener, 100 lbs load capacity
Product Type	"Z" Purl" Hanger, 1" Conduit Size
Special Features	Static Load Capacity 25 Lb

### Manufacturer Information

Brand	Eaton
GTIN	00781011185909
Manufacturers Part Number	BG-16-F13
UPC	781011185909

### Taxonomies, Classifications, and Categories

Category Description	CABLE & PIPE TRANSITS
Type	Hanger



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell  
88101-0000, NM Clovis  
Phone: 575-742-2504  
Fax: 575-742-2508

## Packaging

Carton	1
Package	100
Weight Per each	0.07

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Strctures - Aftermarket
standard	UL/cUL Listed