



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BH4E24 SPRG 1/4", 160LB Rod to BM Hanger, 1/8-1/4 FLNG

Cooper B-Line/Cable Tray

Catalog Number	BH4E24
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series All Threaded Rod and Drop Wire Supports, Hangers, Flange, 1" Height, 1" Length, 1" Width, 0.062LBS, Rod to Beam Hangers, .13" Min Mount Size, .25" Max Mount Size, 0.25" Rod Size, 160 LBS Load Capacity
Weight per unit	0.0006 (lbs/each)
Product Category	Miscellaneous

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
Material	Steel

Material, Color, and Finish

Finish	Zinc Phosphate
--------	----------------

Dimensions and Weight

Size	1/4 In Threaded Rod
------	---------------------

Descriptions

Construction	ONE PIECE
Description	SPRG 1/4",160LB ROD TO BM HANGER,1/8-1/4 FLNG
extra long description	B-LINE BH4-E-2-4 ROD TO BM HANGER,
Features	Whether you are suspending from a ceiling, beam, lathers channel, strut or purlin, Eaton can meet your need with time-saving solutions.
Long Description	Eaton B-Line series all threaded rod and drop wire supports, Hangers, Flange, 1" Height, 1" Length, 1" Width, 0.062lbs, Rod to beam hangers, .13" Min mount size, .25" Max mount size, 0.25" rod size, 160 lbs load capacity
Product Type	Rod to BM Hanger, 1/8" to 1/4" Flange, 1/4" Threaded Rod
Special Features	Static Load Capacity 160 Lb, Flange Thickness 1/8 To 1/4 In, With Thread Impression

Manufacturer Information

Brand	Eaton
GTIN	00781011189808
Manufacturers Part Number	BH4-E-2-4
UPC	781011189808

Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	Rod to beam hanger



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 100

Weight Per each 0.0006

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Lighting and
Lighting ControlsCommercial / Institutional Buildings / Structures
- Commercial / Institutional Buildings / Structures -
OtherCommercial / Institutional Buildings / Structures -
Commercial/Inst Bldg Strctures - Aftermarket

Mounting CHANNEL

standard UL/cUL Listed