

# Specifications



## Eaton BMM603-1SQ

Eaton Bussmann series BMM fuse blocks, 30 A, Single-pole, 200 kA, Screw/quick connect, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series BMM fuse blocks
<b>CATALOG NUMBER</b>	BMM603-1SQ
<b>UPC</b>	051712486446
<b>PRODUCT LENGTH/DEPTH</b>	3 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.065 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Recognized CSA Certified

## Electrical rating

<b>AMPERAGE RATING</b>	30 A
<b>SHORT-CIRCUIT RATING</b>	200 kA
<b>VOLTAGE RATING</b>	600 V

## General information

<b>CONNECTION</b>	Screw/quick connect
-------------------	---------------------

## Physical details

<b>NUMBER OF POLES</b>	Single-pole
------------------------	-------------

## Resources

### CATALOGS

[BMM603-1SQ~MIDGET](#)  
[FUSE BLOCK W/ SCREW](#)  
[and QC - 1 POLE](#)

### CERTIFICATION REPORTS

[Eaton Bussmann EU](#)  
[Declaration of conformity](#)  
[93-68-EEC2308-B](#)

### MULTIMEDIA

[Bussmann series](#)  
[Fuseology](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -](#)  
[BMM603-1SQ](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton BMM603-1SQ

Eaton Bussmann series BMM fuse blocks, 30 A, Single-pole, 200 kA, Screw/quick connect, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series BMM fuse blocks
<b>CATALOG NUMBER</b>	BMM603-1SQ
<b>UPC</b>	051712486446
<b>PRODUCT LENGTH/DEPTH</b>	3 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.065 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Recognized CSA Certified

## Electrical rating

<b>AMPERAGE RATING</b>	30 A
<b>SHORT-CIRCUIT RATING</b>	200 kA
<b>VOLTAGE RATING</b>	600 V

## General information

<b>CONNECTION</b>	Screw/quick connect
-------------------	---------------------

## Physical details

<b>NUMBER OF POLES</b>	Single-pole
------------------------	-------------

## Resources

### CATALOGS

[BMM603-1SQ~MIDGET](#)  
[FUSE BLOCK W/ SCREW](#)  
[and QC - 1 POLE](#)

### CERTIFICATION REPORTS

[Eaton Bussmann EU](#)  
[Declaration of conformity](#)  
[93-68-EEC2308-B](#)

### MULTIMEDIA

[Bussmann series](#)  
[Fuseology](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -](#)  
[BMM603-1SQ](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

