



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2100ST Type BR BRKR100A/2 Pole 120/240V 10K W/Shunt Trip

Eaton Corp

| | |
|------------------|--|
| Catalog Number | BR2100ST |
| Manufacturer | Eaton Corp |
| Description | Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Shunt Trip Circuit Breaker, 100 A, 42 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #4-1/0 Awg Cu/Al, Q28, BR, Type BR Loadcenters, Shunt Trip Included |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | 2 Pole Standard Trip Plug-In |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.2500 IN X 3.0000 IN X 3.0000 IN |
| interrupt rating | 42 kAIC |
| Poles | Two-pole |
| Trip Type | Common breaker trip |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|--|
| Description | TYPE BR BRKR100A/2 POLE 120/240V 10K W/SHUNT TRIP |
| extra long description | ETN BR2100ST BR 100A/2 Pole 120/240 |
| Features | Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF. |
| Long Description | Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on shunt trip circuit breaker, 100 A, 42 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters, Shunt trip included |
| Product Type | BR 100A/2 Pole 120/240V 10K |
| Special Features | Shunt Trip |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676000406 |
| Manufacturers Part Number | BR2100ST |
| UPC | 786676000406 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Specialty Breakers (Quad, Dupl, Shunt Trip) |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 1.2 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - Other |
| standard | UL 489,Federal Specifications Classification W-C375 |