

Specifications



Photo is representative



Eaton BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral

General specifications

| | |
|-----------------------------|-------------------------------|
| PRODUCT NAME | Eaton BR AFCI circuit breaker |
| CATALOG NUMBER | BRP115AF |
| UPC | 786689041014 |
| PRODUCT LENGTH/DEPTH | 2.56 in |
| PRODUCT HEIGHT | 1.1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.38 lb |
| CERTIFICATIONS | UL Listed |

Product specifications

| | |
|----------------------|----------------------------------|
| USED WITH | Type BR Loadcenters |
| AMPERAGE RATING | 15 A |
| VOLTAGE RATING | 120 V |
| NEUTRAL | Plug-on neutral |
| INTERRUPT RATING | 10 kAIC |
| MAIN CIRCUIT BREAKER | BR |
| CONNECTION | Plug-on |
| WIRE SIZE | #14-8 AWG Cu/Al |
| NUMBER OF POLES | Single-pole |
| TYPE | AFCI Combination circuit breaker |
| SPECIAL FEATURES | UL only |

Resources

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral

General specifications

| | |
|----------------------|-------------------------------|
| PRODUCT NAME | Eaton BR AFCI circuit breaker |
| CATALOG NUMBER | BRP115AF |
| UPC | 786689041014 |
| PRODUCT LENGTH/DEPTH | 2.56 in |
| PRODUCT HEIGHT | 1.1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.38 lb |
| CERTIFICATIONS | UL Listed |

Product specifications

| | |
|----------------------|----------------------------------|
| USED WITH | Type BR Loadcenters |
| AMPERAGE RATING | 15 A |
| VOLTAGE RATING | 120 V |
| NEUTRAL | Plug-on neutral |
| INTERRUPT RATING | 10 kAIC |
| MAIN CIRCUIT BREAKER | BR |
| CONNECTION | Plug-on |
| WIRE SIZE | #14-8 AWG Cu/Al |
| NUMBER OF POLES | Single-pole |
| TYPE | AFCI Combination circuit breaker |
| SPECIAL FEATURES | UL only |

Resources

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

