


Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

1510 East Interstate 30 75087-0000, TX Rockwall Phone: 469-913-1945





Special Features

BR2430L125G 125A 1PH LD-CTR 24/30C Nema1 *Eaton Corp*

Catalog Number	BR2430L125G
Manufacturer	Eaton Corp
Description	Eaton BR Style 1-Inch Loadcenter, Main Lug, Ground Bar, 125A, Single-Phase, 30-Pole, 30 Circuits, 24 Spaces, 120/240V, 2/0-#14 Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, G1 Box Size
Weight per unit	24.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen
atures	
amperage rating	125 VAC
Box Size	M104D-731
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX68.5800centimetre
interrupt rating	10 kAIC
main circuit breaker	Environmental Conditions Wet Location; Includes Ground Screv Shape Round
Number of Circuits	30 W
number of spaces	24 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#2/0-300 kcmil Cu/Al at 60°C or 75°C
aterial, Color, and Finish	
Bus Material	Aluminum
Enclosure Material	Metallic
mensions and Weight	
Size	M104D-731
escriptions	
Description	125A 1PH LD-CTR 24/30C NEMA1
extra long description	ETN BR2430L125G BR style 1-inch loa
Long Description	Eaton BR style 1-inch loadcenter, main lug, ground bar, 125A, single-phase, 30-pole, 30 circuits, 24 spaces, 120/240V, 2/0-#14 Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, g1 box size
Product Type	BR Style 1-Inch Loadcenter

Ground bar



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1510 East Interstate 30 75087-0000, TX Rockwall Phone: 469-913-1945 Fax: 469-913-1946

Brand	Eaton	
GTIN	00782116139293	
Manufacturers Part Number	BR2430L125G	
UPC	782116139293	

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL;
-	WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL;
	125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT
	RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Туре	MAIN LUG
unspsc code	39121101

Availability

Status Inactive

Packaging

Carton 1
Weight Per each 24

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50