



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR250B Type BR BRKR 50A/2 Pole 120/240V 10K

Eaton Corp

Catalog Number	BR250B
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, Tapped Molded Opening, Special Application, 50 A, 10 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.5500 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 50A/2 POLE 120/240V 10K
extra long description	ETN BR250B Type BR Breaker 50A/2 Po
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, Tapped molded opening, special application, 50 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR Breaker 50A/2 Pole 120/240V 10K
Special Features	Tapped molded opening, special application

Manufacturer Information

Brand	Eaton
GTIN	00786676003605
Manufacturers Part Number	BR250B
UPC	786676003605

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.55

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489,Federal Specifications Classification W-C375