



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR260H Type BR Breaker 60A/2 Pole 240V 10K

*Eaton Corp*

Catalog Number	BR260H
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On High-Magnetic Circuit Breaker, High-Magnetic, 60 A, 10 Kaic, Two-Pole, 240V, BR, #8-1/0 Awg Cu/Al, BR, Type BR Loadcenters
Weight per unit	0.6000 (lbs/each)
Product Category	2P Special Application Plug-In

### Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	240 V - 240 V

### Descriptions

Description	TYPE BR BREAKER 60A/2 POLE 240V 10K
extra long description	ETN BR260H Type BR Breaker 60A/2 Po
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on high-magnetic circuit breaker, High-magnetic, 60 A, 10 kAIC, Two-pole, 240V, BR, #8-1/0 AWG Cu/Al, BR, Type BR Loadcenters
Product Type	Type BR Breaker 60A/2 Pole 240V 10K
Special Features	High-Magnetic

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786676374606
Manufacturers Part Number	BR260H
UPC	786676374606

### Taxonomies, Classifications, and Categories

Category Description	Breaker Enclosures with or without Breaker
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.6

## Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489,Federal Specifications Classification W-C375