



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR370 Type BR BRKR 70A/3 Pole 240V 10K *Eaton Corp*

Catalog Number	BR370
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 70 A, 10 Kaic, Three-Pole, 240V, BR, Common Breaker Trip, #4-1/0 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

Features

amps	70
dimensions	1.9000 IN X 2.9000 IN X 2.5000 IN
interrupt rating	10 kAIC
pole #	Three
Poles	3
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE BR BRKR 70A/3 POLE 240V 10K
extra long description	ETN BR370 Type BR Breaker 70A/3 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 70 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR Breaker 70A/3 Pole 240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676368001
Manufacturers Part Number	BR370
UPC	786676368001

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	1

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional Energy
standard	UL 489,Federal Specifications Classification W-C375