

Specifications



Photo is representative



Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 125, Plug-on, BRHX

General specifications

PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BRHX2125
UPC	786689041670
PRODUCT LENGTH/DEPTH	3.1 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Product specifications

AMPERAGE RATING	125
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-interchangeable
CIRCUIT BREAKER TYPE	BR
MOUNTING METHOD	Plug-on
INTERRUPT RATING	22 kAIC
MAIN CIRCUIT BREAKER	BR
CONNECTION	Plug-on
NUMBER OF POLES	Two-pole
TRIP RATING	125
TYPE	Quicklag Type BRHX circuit breaker

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRHX2125
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 125, Plug-on, BRHX

General specifications

PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BRHX2125
UPC	786689041670
PRODUCT LENGTH/DEPTH	3.1 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Product specifications

AMPERAGE RATING	125
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-interchangeable
CIRCUIT BREAKER TYPE	BR
MOUNTING METHOD	Plug-on
INTERRUPT RATING	22 kAIC
MAIN CIRCUIT BREAKER	BR
CONNECTION	Plug-on
NUMBER OF POLES	Two-pole
TRIP RATING	125
TYPE	Quicklag Type BRHX circuit breaker

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRHX2125
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

