



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRL220CAF BR Combination Type AfcI 2 Pole 20A 10kaic

Eaton Corp

Catalog Number	BRL220CAF
Manufacturer	Eaton Corp
Description	Eaton BR AfcI Circuit Breaker, Fire-Guard AfcI Combination Circuit Breaker, 20 A, 10 Kaic, Two-Pole, 120 V, 120/240 V, BR, Common Trip, #14-4 Awg Cu/Al, Type BR Loadcenters
Weight per unit	1.0 (lbs/each)
Product Category	In Circuit Breakers

### Features

dimensions	6.0000 IN X 2.5000 IN X 1.2500 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	BR COMBINATION TYPE AFCI 2 POLE 20A 10KAIC
extra long description	ETN BRL220CAF BR 2P AFCI, 20A, 120/
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR AFCI circuit breaker, FIRE-GUARD AFCI Combination circuit breaker, 20 A, 10 kAIC, Two-pole, 120 V, 120/240 V, BR, Common trip, #14-4 AWG Cu/Al, Type BR Loadcenters
Product Type	BR 2P AfcI, 20A, 120/240V, 10kaic
Special Features	Combination arc fault

### Manufacturer Information

Brand	Eaton
GTIN	00786685495163
Manufacturers Part Number	BRL220CAF
UPC	786685495163

### Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	AFCI circuit breakers

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional  
EnergyOtherDatacenters - IT Space: CI and Hyper  
ConvergedMarine Vessels and Equipment - Marine Vessels and  
Equipment - OtherGeneration - Renewable Energy - Alternative  
Energy

standard

UL 1699,Federal Specifications Classification W-C375