

Chimes

Two Entrance Chime Kit

C200 Series

Edwards Chime Kits consist of an Edwards two entrance chime, a 16V transformer, and two push buttons (option of either illuminated or non-illuminated).

Features and Specifications

- Complete installation kit
- Two entrance models
- Illuminated push buttons available
- Available in white or beige
- 75dB at 1m / 65dB at 10 ft.




Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | Color | Transformer | Push Buttons |
|-------------|----------|-------------------|---------|----|-------|-------------|---------------------|
| Chime Kit | C212 | 16V AC | 0.625 A | 10 | Beige | 16V | 2 - non-illuminated |
| | C212-W | 16V AC | 0.625 A | 10 | White | 16V | 2 - non-illuminated |
| | C212-2L | 16V AC | 0.625 A | 10 | Beige | 16V | 2 - illuminated |
| | C212W-2L | 16V AC | 0.625 A | 10 | White | 16V | 2 - illuminated |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| C212 | 1.76 | 1.86 |
| C212-W | 1.76 | 1.86 |
| C212-2L | 1.76 | 1.86 |
| C212W-2L | 1.76 | 1.86 |



Chimes

Two Entrance Chime

C200 Series

The Edwards C200 Series surface mount chimes are specifically designed for low cost installation. They operate from a 16V transformer (purchased separately).

Features and Specifications

- Two entrance models
- Free suspension aluminum tone bars
- Requires no lubrication
- Easy to install
- Available in white or beige




Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | Color | Recommended Transformer |
|--------------------|----------|-------------------|---------|----|-------|-------------------------|
| Two Entrance Chime | C210 | 16V AC | 0.625 A | 10 | Beige | 591 |
| | C210-W | 16V AC | 0.625 A | 10 | White | 591 |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| C210 | 0.94 | 1.02 |
| C210-W | 0.94 | 1.02 |



Chimes

Two Entrance Chime Kit

C200 Series

Edwards Chime Kits consist of an Edwards two entrance chime, a 16V transformer, and two push buttons (option of either illuminated or non-illuminated).

Features and Specifications

- Complete installation kit
- Two entrance models
- Illuminated push buttons available
- Available in white or beige
- 75dB at 1m / 65dB at 10 ft.




Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | Color | Transformer | Push Buttons |
|-------------|----------|-------------------|---------|----|-------|-------------|---------------------|
| Chime Kit | C212 | 16V AC | 0.625 A | 10 | Beige | 16V | 2 - non-illuminated |
| | C212-W | 16V AC | 0.625 A | 10 | White | 16V | 2 - non-illuminated |
| | C212-2L | 16V AC | 0.625 A | 10 | Beige | 16V | 2 - illuminated |
| | C212W-2L | 16V AC | 0.625 A | 10 | White | 16V | 2 - illuminated |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| C212 | 1.76 | 1.86 |
| C212-W | 1.76 | 1.86 |
| C212-2L | 1.76 | 1.86 |
| C212W-2L | 1.76 | 1.86 |



Chimes

Two Entrance Chime

C200 Series

The Edwards C200 Series surface mount chimes are specifically designed for low cost installation. They operate from a 16V transformer (purchased separately).

Features and Specifications

- Two entrance models
- Free suspension aluminum tone bars
- Requires no lubrication
- Easy to install
- Available in white or beige



Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | Color | Recommended Transformer |
|--------------------|----------|-------------------|---------|----|-------|-------------------------|
| Two Entrance Chime | C210 | 16V AC | 0.625 A | 10 | Beige | 591 |
| | C210-W | 16V AC | 0.625 A | 10 | White | 591 |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| C210 | 0.94 | 1.02 |
| C210-W | 0.94 | 1.02 |

