



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT4SM BT4SM Cable Tie Bulk-PK

Panduit Corporation

Catalog Number	BT4SM
Manufacturer	Panduit Corporation
Description	The BT4S-M Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Standard Cross Section, 15.1" (384MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 1000.
Weight per unit	1.0 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	15.1
Thickness	0.05

Descriptions

Description	BT4SM CABLE TIE BULK-PK
extra long description	PAN BT4S-M Dome-Top® BT4S-M Barb Ti
Long Description	The BT4S-M Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Standard cross section, 15.1" (384mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 1000.
Product Type	Dome-Top® BT4S-M Barb Tie, PA6.6, 15.1"L, 50LB, PK1000
Special Features	Indoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983412426
Manufacturers Part Number	BT4S-M
UPC	074983412426



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Packaging

Carton	1
Package	1000
Weight Per each	1

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275 (File 31212), Cert 05968/C0, BV File ACE 14/601/01 Product Code: 2535H, 89/60111 (E3), 11130200, QPL-AS23190, RoHS Compliant
----------	--