

# Specifications



Photo is representative



## Eaton C25DNF330A

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 110/120 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

|                             |                                  |
|-----------------------------|----------------------------------|
| <b>PRODUCT NAME</b>         | Eaton definite purpose contactor |
| <b>CATALOG NUMBER</b>       | C25DNF330A                       |
| <b>UPC</b>                  | 782116300594                     |
| <b>PRODUCT LENGTH/DEPTH</b> | 3.35 in                          |
| <b>PRODUCT HEIGHT</b>       | 3.75 in                          |
| <b>PRODUCT WIDTH</b>        | 2.4 in                           |
| <b>PRODUCT WEIGHT</b>       | 1.05 lb                          |
| <b>WARRANTY</b>             | 1 year                           |
| <b>COMPLIANCES</b>          | RoHS Compliant                   |
| <b>CERTIFICATIONS</b>       | UL Recognized<br>CSA Certified   |
| <b>PRODUCT TYPE</b>         | Definite purpose contactor       |



Powering Business Worldwide

## Product specifications

|                            |  |
|----------------------------|--|
| <b>AMPERAGE RATING</b>     | 30A  |
| <b>NUMBER OF POLES</b>     | Three-pole   |
| <b>TYPE</b>                | Non-reversing  |
| <b>COIL</b>                | 208-240 Vac, 50/60 Hz  |
| <b>ENCLOSURE</b>           | Open with metal mounting plate   |
| <b>FRAME SIZE</b>          | 15-50 A, two-pole and three-pole   |
| <b>INDUCTIVE FULL LOAD</b> | 30 A   |
| <b>MODEL</b>               | Contactator  |
| <b>RESISTIVE LOAD</b>      | 40 A   |
| <b>TERMINALS</b>           | Box lugs (posidrive setscrew) and quick connect terminals (side-by-side) |
| <b>CONNECTION</b>          | Quick  |

## Resources

|                               |   |
|-------------------------------|---|
| CATALOGS                      | <a href="#">Motor Control and Protection, Definite Purpose Contactors and Starters, Volume 5, Tab 4</a> |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - C25DNF330A</a>  |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

