



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DND240A Open N-R 2P 40A DP Cont SCR/PP W/QC Term 120VAC CO Eaton Corp

Catalog Number	C25DND240A
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 110-120 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, Two-Pole, 50A, Screw/Pressure Plate and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 3.7500 IN
Enclosure Type	Open with metal mounting plate

### Descriptions

Description	OPEN N-R 2P 40A DP CONT SCR/PP W/QC TERM 120VAC CO
extra long description	ETN C25DND240A OP N-R 2P 40ADPCNT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 40A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Two-pole, 50A, Screw/pressure plate and quick connect terminals (side-by-side), Non-reversing
Product Type	Op N-R 2P 40ADPCNT SCR/PP W/Qc120ac

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300389
Manufacturers Part Number	C25DND240A
UPC	782116300389

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL Recognized, CSA Certified, RoHS Compliant