



Powering Business Worldwide

pe.eaton.com

C440 Electronic Overload Relay - NEMA

C440A1A045SAX

UPC:786685412375

Dimensions:

- **Height:** X
- **Length:** 4.32 IN
- **Width:** 1.8 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Reset:** Selectable Auto/Manual
- **Frame Size:** 45mm
- **Overload Range:** 9-45A
- **Size:** Separate Mount
- **Special Features:** Standard
- **Trip Type:** Selectable 10A, Class 10 ,20, 30
- **Type:** Electronic overload relay

Supporting documents:

- [C440 Electronic Overload Relay](#)
- [Eatons Volume 5-Motor Control and Protection](#)
- [C440A_AX 2D Drawing Xchange](#)
- [C440A_AX AutoCAD 2D Footprint \(mm\)](#)
- [C440A_AX 2D PDF](#)
- [C440A_AX 3D Inventor](#)
- [C440A_AX 3D Model Xchange](#)
- [C440 NEMA Electronic Overload - Self Powered](#)
- [Eaton Specification Sheet - C440A1A045SAX](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

C440 Electronic Overload Relay - NEMA

C440A1A045SAX

UPC:786685412375

Dimensions:

- **Height:** X
- **Length:** 4.32 IN
- **Width:** 1.8 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Reset:** Selectable Auto/Manual
- **Frame Size:** 45mm
- **Overload Range:** 9-45A
- **Size:** Separate Mount
- **Special Features:** Standard
- **Trip Type:** Selectable 10A, Class 10 ,20, 30
- **Type:** Electronic overload relay

Supporting documents:

- [C440 Electronic Overload Relay](#)
- [Eatons Volume 5-Motor Control and Protection](#)
- [C440A_AX 2D Drawing Xchange](#)
- [C440A_AX AutoCAD 2D Footprint \(mm\)](#)
- [C440A_AX 2D PDF](#)
- [C440A_AX 3D Inventor](#)
- [C440A_AX 3D Model Xchange](#)
- [C440 NEMA Electronic Overload - Self Powered](#)
- [Eaton Specification Sheet - C440A1A045SAX](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.