

RATCHETING CABLE CUTTER



The hardened steel blades on this heavy duty cutter ensure consistent cuts and long-term durability, while the rounded blade design minimizes cable distortion during cutting.

- Replaceable hardened steel blades provide long lasting cutting of copper and aluminum cables
- Cuts up to 750 kcmil copper and 1000 kcmil aluminum cables
- Two-step ratcheting mechanism for fewer strokes per cut
- Quick-release lever opens blade at any time during operation
- Molded grip for comfort, stability and leverage when making cuts

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION			
CCPR400	582777	Ratcheting Cable Cutter			
		HEIGHT	WIDTH	DEPTH	WEIGHT
CCPR400		10.25"	5.5"	1.25"	31 oz
*MAXIMUM CUTTING POWER (COPPER)			*MAXIMUM CUTTING POWER (ALUMINUM)		
750 kcmil(MCM)			1000 kcmil(MCM)		

*Note: Maximum cutting capacity is for single conductor wires

CABLE RIPPING TOOL



This NM-B cable ripper makes cable jacket removal quick and easy. It slits the cable jacket with one easy stroke. Includes convenient wire gauging holes in the handle.

- Makes end or mid-run slits to expose insulated wires
- Easily slits the outer jacket on NM-B cable
- Accurate wire measuring gauge holes - 6 to 14 AWG solid wire

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION
CRT	582933	Cable Ripper Tool

BOOT KNIFE



Our tough boot knife cuts electronic wire, telephone cables and skin cable jackets.

- Tough forged steel blade
- Use to cut electronic wire, telephone cables, & skin cable jackets
- Ergonomic handle for snug, solid grip
- Comes with protective storage cap

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION			
BN01	582884	Boot Knife			
		HEIGHT	WIDTH	DEPTH	WEIGHT
BN01		6.38"	1"	0.5"	2 oz

RATCHETING CABLE CUTTER



The hardened steel blades on this heavy duty cutter ensure consistent cuts and long-term durability, while the rounded blade design minimizes cable distortion during cutting.

- Replaceable hardened steel blades provide long lasting cutting of copper and aluminum cables
- Cuts up to 750 kcmil copper and 1000 kcmil aluminum cables
- Two-step ratcheting mechanism for fewer strokes per cut
- Quick-release lever opens blade at any time during operation
- Molded grip for comfort, stability and leverage when making cuts

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION		
CCPR400	582777	Ratcheting Cable Cutter		
		HEIGHT	WIDTH	DEPTH
CCPR400		10.25"	5.5"	1.25"
		*MAXIMUM CUTTING POWER (COPPER)		*MAXIMUM CUTTING POWER (ALUMINUM)
		750 kcmil(MCM)		1000 kcmil(MCM)

*Note: Maximum cutting capacity is for single conductor wires

CABLE RIPPING TOOL



This NM-B cable ripper makes cable jacket removal quick and easy. It slits the cable jacket with one easy stroke. Includes convenient wire gauging holes in the handle.

- Makes end or mid-run slits to expose insulated wires
- Easily slits the outer jacket on NM-B cable
- Accurate wire measuring gauge holes - 6 to 14 AWG solid wire

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION
CRT	582933	Cable Ripper Tool

BOOT KNIFE



Our tough boot knife cuts electronic wire, telephone cables and skin cable jackets.

- Tough forged steel blade
- Use to cut electronic wire, telephone cables, & skin cable jackets
- Ergonomic handle for snug, solid grip
- Comes with protective storage cap

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION		
BN01	582884	Boot Knife		
		HEIGHT	WIDTH	DEPTH
BN01		6.38"	1"	0.5"
		WEIGHT		
		2 oz		