

Specifications



Photo is representative



Eaton CCP2R-2-30CC

Eaton Bussmann series CCP UL98 fusible disconnect, 600 Vac, 125 Vdc, 30A, UL98 fusible disconnect, Two-pole, 60 Hz, Class CC, 200 - CCP2R-2-30CC

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
---------------------	---

CATALOG NUMBER	CCP2R-2-30CC
-----------------------	--------------

UPC	051712709682
------------	--------------

PRODUCT LENGTH/DEPTH	1.9 in
-----------------------------	--------

PRODUCT HEIGHT	3.7 in
-----------------------	--------

PRODUCT WIDTH	0.3 in
----------------------	--------

PRODUCT WEIGHT	1.18 lb
-----------------------	---------

WARRANTY	Not Applicable
-----------------	----------------

CERTIFICATIONS	Contact Manufacturer
-----------------------	----------------------



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	30A
FREQUENCY RATING	60 Hz
SHORT-CIRCUIT RATING	200 kAIC
VOLTAGE RATING	600 Vac, 125 Vdc

General information

SUITABLE FOR FUSES	LP-CC-1/2 to LP-CC-30 KTK-R-1/10 to KTK-R-30 FNQ-R-1/4 to FNQ-R-30
--------------------	--

Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Two-pole

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 CCP2R-2-30CC~2 Pole Comp Ckt Protect 30A
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2512
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP2R-2-30CC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton CCP2R-2-30CC

Eaton Bussmann series CCP UL98 fusible disconnect, 600 Vac, 125 Vdc, 30A, UL98 fusible disconnect, Two-pole, 60 Hz, Class CC, 200 - CCP2R-2-30CC

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
---------------------	---

CATALOG NUMBER	CCP2R-2-30CC
-----------------------	--------------

UPC	051712709682
------------	--------------

PRODUCT LENGTH/DEPTH	1.9 in
-----------------------------	--------

PRODUCT HEIGHT	3.7 in
-----------------------	--------

PRODUCT WIDTH	0.3 in
----------------------	--------

PRODUCT WEIGHT	1.18 lb
-----------------------	---------

WARRANTY	Not Applicable
-----------------	----------------

CERTIFICATIONS	Contact Manufacturer
-----------------------	----------------------



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	30A
FREQUENCY RATING	60 Hz
SHORT-CIRCUIT RATING	200 kAIC
VOLTAGE RATING	600 Vac, 125 Vdc

General information

SUITABLE FOR FUSES	LP-CC-1/2 to LP-CC-30 KTK-R-1/10 to KTK-R-30 FNQ-R-1/4 to FNQ-R-30
--------------------	--

Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Two-pole

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 CCP2R-2-30CC~2 Pole Comp Ckt Protect 30A
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2512
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP2R-2-30CC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

