



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CG906275 3/4" Alu 90D Cord Conn *Appleton/Oz Gedney*

Catalog Number	CG906275
Manufacturer	Appleton/Oz Gedney
Description	90 Deg Liquidtight Strain Relief Connector, Size: 3/4 In, Conductor Range: 5/8 - 3/4 In, Material: Cast Aluminum, Color: Orange Label, Nema Rating: Nema 3R, Connection: Threaded Hub, Standard: Class I, Division 2, Class II, Division 1 A
Weight per unit	0.1600 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Threaded Hub
------------	--------------

Material, Color, and Finish

Color	/;Orange
-------	----------

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4" ALU 90D CORD CONN
extra long description	APP CG90-6275 3/4 IN ALUM L-T CRD&C
Long Description	90 DEG Liquidtight Strain Relief Connector, Size: 3/4 IN, Conductor Range: 5/8 - 3/4 IN, Material: Cast Aluminum, Color: Orange Label, Nema Rating: NEMA 3R, Connection: Threaded Hub, Standard: Class I, Division 2, Class II, Division 1 A
Product Type	3/4 In Alum L-T CRD&CBL Conn
Special Features	Color coded identification label clearly states the catalog number and minimum-maximum cable diameter range for which the connector is designed;Copper free (4/10 of 1 PCT or less) aluminum cap;For use in wet or dry locations sealing electrical connections against dust and dirt, oil, water or other atmosphere containing moisture;Neoprene sealing grommet;Neoprene sealing grommet firmly but safely grips cable jacket providing strain relief while protecting internal wiring connections against external tension

Manufacturer Information

Brand	Appleton
GTIN	00781381189859
Manufacturers Part Number	CG90-6275
UPC	781381189859



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	90 DEG Liquidtight Strain Relief Connector

Packaging

Carton	1
Package	25
Weight Per each	0.16

Uses, Certifications, and Standards

Application	For Flexible Type Neoprene, Hypalon And PVC Jacketed Power Or Control Cord And Cable
nema rating	3R
standard	Class I, Division 2, Class II, Division 1 And 2 Class III, UL 514B, E14817, CSA C22.2 No. 18.3, 065178