



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH30L3225R 3PH/CH Loadctr 225A Mlo 30 Cir. Cu Bus Nema 3R

Eaton Corp

Catalog Number	CH30L3225R
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenter, Standard, Main Lug Only, 225 A, D, Copper, Nema 3R, Metallic, Overhead, CH, 30 Circuits, 30 Spaces, Four-Wire, Three-Phase, #4 Awg-300 Kcmil
Weight per unit	36.7 (lbs/each)
Product Category	Three Phase Main Lug Load Cent

Features

amperage rating	225
interrupt rating	35
media	Yes
number of spaces	30
Phase	3

Dimensions and Weight

Depth	29.13
Height	5.19
Size	D
Width	14.31

Descriptions

Description	3PH/CH LOADCNTR 225A MLO 30 CIR. CU BUS NEMA 3R
extra long description	ETN CH30L3225R 3Ph/CH LC 225A MLO 3
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenter,Standard,Main lug only,225 A,D,Copper,NEMA 3R,Metallic,Overhead,CH,30 Circuits,30 Spaces,Four-wire,Three-phase,#4 AWG-300 kcmil
Product Type	3PH/CH LC 225A Mlo 30 CKT Cu Bus N3R
Special Features	Standard

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113097930
Manufacturers Part Number	CH30L3225R
UPC	782113097930



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Main lug loadcenter

Packaging

Carton 1

Weight Per each 36.7

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard UL 67,UL 50