

Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH spa panel	CH50SPAST
UPC	Product Length/Depth
786685969893	3.13 in
Product Height	Product Width
4.5 in	4.5 in
Product Weight	Warranty
7.35 lb	Limited lifetime
Certifications	Catalog Notes
Contact Manufacturer	Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature

Product specifications

Type

Ch spa panel-quick pro

Amperage Rating

50A

Number of circuits

50

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH spa panel	CH50SPAST
UPC	Product Length/Depth
786685969893	3.13 in
Product Height	Product Width
4.5 in	4.5 in
Product Weight	Warranty
7.35 lb	Limited lifetime
Certifications	Catalog Notes
Contact Manufacturer	Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature

Product specifications

Type

Ch spa panel-quick pro

Amperage Rating

50A

Number of circuits

50

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)