



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## CH115CAF 1P 15A 120/240V Combination Arc Fault Breaker

*Eaton Corp*

Catalog Number	CH115CAF
Manufacturer	Eaton Corp
Description	Special Application Circuit Breaker, Thermal Magnetic; 1 Pole; 120/240 Vac; 15 Ampere; Interrupting Rating 10000 Ampere; Box Lug Terminal; Wire Size (2) 14 to 10 Awg (Aluminum/Copper), (1) 14 to 8 Awg (Aluminum/Copper); Application Hacr
Weight per unit	0.7800 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

### Features

Clamp Type	FNQ-5
Construction Feature	ARC FAULT CIRCUIT INTERRUPTER
Current Rating	15 AMPERE
Interrupting Rating	10000 AMPERE
Knockout Location	08526700397
Number of Knockouts	1
Poles	1 PH
Terminal Type	BOX LUG
Voltage Rating	120/240 VAC
Wire Size	(2) 14 TO 10 AWG (ALUMINUM/COPPER), (1) 14 TO 8 AWG (ALUMINUM/COPPER)

### Dimensions and Weight

Depth in inch	Loadcenter
Diameter	Thermal Magnetic
Diameter in inch	3/4 Inch W
Size	3/4 INCH W

### Descriptions

Commodity Description	1 POLE STANDARD TRIP PLUG-IN CIRCUIT BREAKERS
Description	1P 15A 120/240V COMBINATION ARC FAULT BREAKER
Long Description	SPECIAL APPLICATION CIRCUIT BREAKER, THERMAL MAGNETIC; 1 POLE; 120/240 VAC; 15 AMPERE; INTERRUPTING RATING 10000 AMPERE; BOX LUG TERMINAL; WIRE SIZE (2) 14 TO 10 AWG (ALUMINUM/COPPER), (1) 14 TO 8 AWG (ALUMINUM/COPPER); APPLICATION HACR
Product Type	Special Application Circuit Breaker

### Manufacturer Information

Brand	FIRE-GUARD[TM]
Manufacturers Part Number	CH115CAF



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fault Sensing Breakers (AFCI/GFCI)  
Type ..... THERMAL MAGNETIC

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1  
Weight Per each ..... 0.78

## Uses, Certifications, and Standards

Application ..... HACR  
Approval ..... UL 1699, CSA  
Mounting ..... PLUG ON  
Used On ..... LOAD CENTER, PANEL