



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH335 Type CH BRKR 35A/3 Pole 240V 10K

Eaton Corp

Catalog Number	CH335
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CH 3/4-Inch Standard Circuit Breaker, 35 A, 10 Kaic, Three-Pole, 240V, CH, Common Breaker Trip, #14-6 Awg Cu/Al, CH, Type CH Loadcenters
Weight per unit	0.8600 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

Features

dimensions	3.5000 IN X 2.2500 IN X 3.5000 IN
interrupt rating	10 kAIC
Poles	Three-pole
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE CH BRKR 35A/3 POLE 240V 10K
extra long description	ETN CH335 Type CH Breaker 35A/3 Pol
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 35 A, 10 kAIC, Three-pole, 240V, CH, Common breaker trip, #14-6 AWG Cu/Al, CH, Type CH Loadcenters
Product Type	Type CH Breaker 35A/3 Pole 240V 10K

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113316994
Manufacturers Part Number	CH335
UPC	782113316994

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.86

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional Energy
standard	UL 489