

# Specifications

## Eaton CHEC42N225LRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 42 Circuits



### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC42N225LRNSP
<b>UPC</b>	782116984176
<b>PRODUCT LENGTH/DEPTH</b>	39.5 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	24 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8LS or CHSUR8LF separately

## Product specifications

<b>SPECIAL FEATURES</b>	Includes renovation terminal blocks
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	42
<b>NUMBER OF SPACES</b>	42
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC42N225LRNSP</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton CHEC42N225LRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 42 Circuits



### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC42N225LRNSP
<b>UPC</b>	782116984176
<b>PRODUCT LENGTH/DEPTH</b>	39.5 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	24 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8LS or CHSUR8LF separately



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Includes renovation terminal blocks
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	42
<b>NUMBER OF SPACES</b>	42
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC42N225LRNSP</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

