

# Eaton CHFGF115

Catalog Number: CHFGF115

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, Trip flag, GFCI, 15 A, 10 kAIC, Single-pole, 120/240 V, CHFGF, Ground fault circuit interrupter, GFI



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH GFCI circuit breaker	CHFGF115
<b>UPC</b>	<b>Product Length/Depth</b>
786685546216	3.5 in
<b>Product Height</b>	<b>Product Width</b>
1.5 in	6 in
<b>Product Weight</b>	<b>Warranty</b>
1 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Switching Duty Rated, HACR Rated

## Product specifications

### Type

Ground fault circuit breaker

### Special features

Trip flag, GFCI

### Amperage Rating

15 A

### Voltage rating

120/240 V

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Interrupt rating

10 kAIC

### Main circuit breaker

CHFGF

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHFGF115](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHFGF115

Catalog Number: CHFGF115

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, Trip flag, GFCI, 15 A, 10 kAIC, Single-pole, 120/240 V, CHFGF, Ground fault circuit interrupter, GFI



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH GFCI circuit breaker	CHFGF115
<b>UPC</b>	<b>Product Length/Depth</b>
786685546216	3.5 in
<b>Product Height</b>	<b>Product Width</b>
1.5 in	6 in
<b>Product Weight</b>	<b>Warranty</b>
1 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Switching Duty Rated, HACR Rated

## Product specifications

### Type

Ground fault circuit breaker

### Special features

Trip flag, GFCI

### Amperage Rating

15 A

### Voltage rating

120/240 V

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Interrupt rating

10 kAIC

### Main circuit breaker

CHFGF

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHFGF115](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)