

Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH AFCI circuit breaker	CHFCAF120PN
UPC	Product Length/Depth
786685546209	3.5 in
Product Height	Product Width
3 in	1 in
Product Weight	Warranty
0.5 lb	Limited lifetime
Compliances	Certifications
HACR Rated	UL Listed

Catalog Notes

Switching Duty Rated, HACR Rated

Product specifications

Used with

Type CH Loadcenters

Type

AFCI Branch feeder circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Pigtail

Number of poles

Single-pole

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH AFCI circuit breaker	CHFCAF120PN
UPC	Product Length/Depth
786685546209	3.5 in
Product Height	Product Width
3 in	1 in
Product Weight	Warranty
0.5 lb	Limited lifetime
Compliances	Certifications
HACR Rated	UL Listed

Catalog Notes

Switching Duty Rated, HACR Rated

Product specifications

Used with

Type CH Loadcenters

Type

AFCI Branch feeder circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Pigtail

Number of poles

Single-pole

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)