

Specifications

Eaton CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative



General specifications

PRODUCT NAME	Eaton CH AFCI circuit breaker
CATALOG NUMBER	CHFCAF120PN
UPC	786685546209
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Limited lifetime
COMPLIANCES	HACR Rated
CERTIFICATIONS	UL Listed
CATALOG NOTES	Switching Duty Rated, HACR Rated



Powering Business Worldwide

Product specifications

USED WITH	Type CH Loadcenters
TYPE	AFCI Branch feeder circuit breaker
AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
NEUTRAL	Plug-on neutral
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	CH
CONNECTION	Pigtail
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHFCAF120PN
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative



General specifications

PRODUCT NAME	Eaton CH AFCI circuit breaker
CATALOG NUMBER	CHFCAF120PN
UPC	786685546209
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Limited lifetime
COMPLIANCES	HACR Rated
CERTIFICATIONS	UL Listed
CATALOG NOTES	Switching Duty Rated, HACR Rated



Powering Business Worldwide

Product specifications

USED WITH	Type CH Loadcenters
TYPE	AFCI Branch feeder circuit breaker
AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
NEUTRAL	Plug-on neutral
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	CH
CONNECTION	Pigtail
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHFCAF120PN
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

