

# Specifications

## Eaton CHFGFT130

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, 30 A, 10 kAIC, Single-pole, CHFGF, Plug-on, Ground fault circuit interrupter, GF with flag



Photo is representative



### General specifications

PRODUCT NAME	Eaton CH GFCI circuit breaker
CATALOG NUMBER	CHFGFT130
UPC	786680117527
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	1.3 lb
CERTIFICATIONS	UL 489



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault circuit breaker
<b>AMPERAGE RATING</b>	30 A
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GF with flag
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFGF
<b>CONNECTION</b>	Plug-on
<b>NUMBER OF POLES</b>	Single-pole

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHFGFT130](#)

### WARRANTY GUIDES

[Eaton type CH circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CHFGFT130

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, 30 A, 10 kAIC, Single-pole, CHFGF, Plug-on, Ground fault circuit interrupter, GF with flag



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton CH GFCI circuit breaker
<b>CATALOG NUMBER</b>	CHFGFT130
<b>UPC</b>	786680117527
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.1 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	1.3 lb
<b>CERTIFICATIONS</b>	UL 489



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault circuit breaker
<b>AMPERAGE RATING</b>	30 A
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GF with flag
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFGF
<b>CONNECTION</b>	Plug-on
<b>NUMBER OF POLES</b>	Single-pole

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHFGFT130](#)

### WARRANTY GUIDES

[Eaton type CH circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

