

Specifications



Eaton CHSPTELE

CHSP Service Entrance Protection
Accessories, Type 2 Quick Connect design, 20
kAIC

General specifications

PRODUCT NAME	Eaton surge protection
CATALOG NUMBER	CHSPTELE
UPC	786685436913
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	0.58 in
PRODUCT WEIGHT	5.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 6500
CATALOG NOTES	20 kA per line current capacity. 230 Vdc breakdown voltage. Indoor installation or rain-tight when used with recommended enclosure.



Powering Business Worldwide

Product specifications

TYPE	Type 2 Quick Connect design
SPECIAL FEATURES	Add additional AC and cable protection modules, protects four telephone lines

Resources

CATALOGS	Residential and Light Commercial, Surge Protection, Volume 1 Tab 2
-----------------	--

VOLTAGE RATING

90-120 Vac, 48-52 Vdc

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
CHSPTELE](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications



Eaton CHSPTELE

CHSP Service Entrance Protection
Accessories, Type 2 Quick Connect design, 20
kAIC

General specifications

PRODUCT NAME	Eaton surge protection
CATALOG NUMBER	CHSPTELE
UPC	786685436913
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	0.58 in
PRODUCT WEIGHT	5.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 6500
CATALOG NOTES	20 kA per line current capacity. 230 Vdc breakdown voltage. Indoor installation or rain-tight when used with recommended enclosure.



Powering Business Worldwide

Product specifications

TYPE	Type 2 Quick Connect design
SPECIAL FEATURES	Add additional AC and cable protection modules, protects four telephone lines

Resources

CATALOGS	Residential and Light Commercial, Surge Protection, Volume 1 Tab 2
-----------------	--

VOLTAGE RATING

90-120 Vac, 48-52 Vdc

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
CHSPTELE](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

