



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHR3G9N9NS Metered-Ringless Pop Surface

Eaton Corp

Catalog Number	CHR3G9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: Non-GND Fault, Weather and Tamper Resist Center and Right Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 14-30R, Right: Nema 5-20R2GFI WR TR, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Dimensions and Weight

Depth	31
Height	7.5
Width	10

### Descriptions

Description	METERED-RINGLESS POP SURFACE
extra long description	ETN CHR3G9N9NS METERED-RINGLESS POP
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Weather and tamper resist center and right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 14-30R, Right: NEMA 5-20R2GFI WR TR, Ringless
Product Type	Metered-Ringless Pop, Surface
Special Features	Water and tamper resistant center/right receptacle

### Manufacturer Information

Brand	Eaton
GTIN	00786685552743
Manufacturers Part Number	CHR3G9N9NS
UPC	786685552743

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered

### Packaging

Carton	1
Weight Per each	30



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting standard	SURFACE UL Listed file E163588,UL 231