



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CL900 Digital Clamp Meter, Ac Auto-Range TRMS

*Klein Tools*

Catalog Number	CL900
Manufacturer	Klein Tools
Description	The CL900 Electrical Tester Is An Auto-Ranging, True Root Mean Square (TRMS) Digital Clamp Meter. It Measures Ac/DC Current Via The Clamp and Measures Ac/DC Voltage, Resistance, Continuity, Frequency, Duty-Cycle, Capacitance, and Tests Diodes Via Test-Leads. It Features A Low Impedance (Loz) Mode For Identifying and Eliminating Ghost or Stray Voltages, and Has A Dedicated Mode For Capturing Inrush Current.
Weight per unit	1.1 (lbs/each)
Product Category	Meters, Panel Instruments

### Features

ac voltage	1000
auto-power off	Yes
Capacitance	6000 $\mu$ F
display	6000 Count LCD
functions	Audible Continuity, Capacitance, Diode Test, Frequency & Duty Cycle, Min/Max feature, Data Hold capability, Inrush Current, Low Impedance
included	Carrying Case, Instruction Manual, Straight Input Test Leads, Batteries
Material	Plastic/Electronics
media	Yes
Overall Height	1.70" (4.3 cm)
Overall Width	3.90" (9.9 cm)
Temperature Range	—
Voltage	1000V AC/DC

### Dimensions and Weight

Overall Length	10.39" (26.4 cm)
----------------	------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DIGITAL CLAMP METER, AC AUTO-RANGE TRMS
extra long description	KLEIN CL900 2000A Digital Clamp Met
Features	The CL900 Electrical Tester is an auto-ranging, true root mean square (TRMS) digital clamp meter. It measures AC/DC current via the clamp and measures AC/DC voltage, resistance, continuity, frequency, duty-cycle, capacitance, and tests diodes via test-leads. It features a Low Impedance (LoZ) mode for identifying and eliminating ghost or stray voltages, and has a dedicated mode for capturing Inrush Current.
Long Description	The CL900 Electrical Tester is an auto-ranging, true root mean square (TRMS) digital clamp meter. It measures AC/DC current via the clamp and measures AC/DC voltage, resistance, continuity, frequency, duty-cycle, capacitance, and tests diodes via test-leads. It features a Low Impedance (LoZ) mode for identifying and eliminating ghost or stray voltages, and has a dedicated mode for capturing Inrush Current.
Product Type	2000A Digital Clamp Meter
Special Features	Low Impedance (LoZ) Mode; Dedicated Mode for Capturing Inrush Current; Integrated Non-Contact Voltage Tester

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644692352
Manufacturers Part Number	CL900
UPC	092644692352

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	CLAMP METER

## Packaging

Carton	1
Weight	17.6 oz (499 g)
Weight Per each	1.1

## Uses, Certifications, and Standards

Application	Measures Current to 2000A AC/DC
standard	CAT IV 600V, CAT III 1000V