



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL900 Digital Clamp Meter, Ac Auto-Range TRMS

Klein Tools

Catalog Number	CL900
Manufacturer	Klein Tools
Description	The CL900 Electrical Tester Is An Auto-Ranging, True Root Mean Square (TRMS) Digital Clamp Meter. It Measures Ac/DC Current Via The Clamp and Measures Ac/DC Voltage, Resistance, Continuity, Frequency, Duty-Cycle, Capacitance, and Tests Diodes Via Test-Leads. It Features A Low Impedance (Loz) Mode For Identifying and Eliminating Ghost or Stray Voltages, and Has A Dedicated Mode For Capturing Inrush Current.
Weight per unit	1.1 (lbs/each)
Product Category	Meters, Panel Instruments

Features

ac voltage	1000
auto-power off	Yes
Capacitance	6000 μ F
display	6000 Count LCD
functions	Audible Continuity, Capacitance, Diode Test, Frequency & Duty Cycle, Min/Max feature, Data Hold capability, Inrush Current, Low Impedance
included	Carrying Case, Instruction Manual, Straight Input Test Leads, Batteries
Material	Plastic/Electronics
media	Yes
Overall Height	1.70" (4.3 cm)
Overall Width	3.90" (9.9 cm)
Temperature Range	—
Voltage	1000V AC/DC

Dimensions and Weight

Overall Length	10.39" (26.4 cm)
----------------	------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DIGITAL CLAMP METER, AC AUTO-RANGE TRMS
extra long description	KLEIN CL900 2000A Digital Clamp Met
Features	The CL900 Electrical Tester is an auto-ranging, true root mean square (TRMS) digital clamp meter. It measures AC/DC current via the clamp and measures AC/DC voltage, resistance, continuity, frequency, duty-cycle, capacitance, and tests diodes via test-leads. It features a Low Impedance (LoZ) mode for identifying and eliminating ghost or stray voltages, and has a dedicated mode for capturing Inrush Current.
Long Description	The CL900 Electrical Tester is an auto-ranging, true root mean square (TRMS) digital clamp meter. It measures AC/DC current via the clamp and measures AC/DC voltage, resistance, continuity, frequency, duty-cycle, capacitance, and tests diodes via test-leads. It features a Low Impedance (LoZ) mode for identifying and eliminating ghost or stray voltages, and has a dedicated mode for capturing Inrush Current.
Product Type	2000A Digital Clamp Meter
Special Features	Low Impedance (LoZ) Mode; Dedicated Mode for Capturing Inrush Current; Integrated Non-Contact Voltage Tester

Manufacturer Information

Brand	Klein Tools
GTIN	00092644692352
Manufacturers Part Number	CL900
UPC	092644692352

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	CLAMP METER

Packaging

Carton	1
Weight	17.6 oz (499 g)
Weight Per each	1.1

Uses, Certifications, and Standards

Application	Measures Current to 2000A AC/DC
standard	CAT IV 600V, CAT III 1000V