



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CR15LA Comm Recp 15A/125V La *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | CR15LA |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V |
| Weight per unit | 0.1956 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 15 |
| connection | Side wire |
| Dielectric Strength | Withstands 1500V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3 |
| Outlet Type | Indoor, Commercial |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .780 |

Descriptions

| | |
|------------------------|---|
| Description | COMM RECP 15A/125V LA |
| extra long description | P&S CR15LA COMMERCIAL RECEPTACLE 15 |
| Long Description | Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V |
| Product Type | Commercial Receptacle 15A/125V La |
| Special Features | Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive termina |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007608038 |
| Manufacturers Part Number | CR15-LA |
| UPC | 785007608038 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.1956 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 50° C |