



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS320GY Switch, Spec, 3W, 20A 120/277V, Gy *Hubbell Wiring Devices*

| | |
|------------------|---|
| Catalog Number | CS320GY |
| Manufacturer | Hubbell Wiring Devices |
| Description | Toggle Switch, Commercial Grade, Three Way, 20A 120/277V Ac, Side Wired |
| Weight per unit | 0.0750 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------------|-----------------|
| action | SPDT |
| amperage rating | 20 |
| connection | Side Wired Only |
| Contact Configuration | Two Position |
| Contact Rating | Per UL 20 |
| Current Rating | 20 |
| insulation | False |
| Material | Nylon |
| operating cycles | 50,000 |
| pallet quantity | 4500 |
| Poles | Single Pole |
| Switch Type | Toggle |
| Voltage Rating | 120-277 |
| Wattage | 5540 |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 4.18 in x 1.49 in x 1.83 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|---|
| Description | SWITCH, SPEC, 3W, 20A 120/277V, GY |
| extra long description | HWDK CS320GY SWITCH, SPEC, 3W, 20A |
| Long Description | Toggle Switch, Commercial Grade, Three Way, 20A 120/277V AC, Side Wired |
| Product Type | Switch, Spec, 3W, 20A 120/277V, Gy |
| Special Features | Standard Product |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585902272 |
| Manufacturers Part Number | CS320GY |
| series | General Purpose |
| UPC | 783585902272 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | TOGGLE |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.075 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial Spec Grade |
| Enclosure | None |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| standard | UL Listed |