



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS6375 LKG Inlt, 50A 125/250V, 3P4W Hubbell Wiring Devices

|                  |  |
|------------------|--|
| Catalog Number   | CS6375   |
| Manufacturer     | Hubbell Wiring Devices   |
| Description      | Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V Ac, 3-Pole 4-Wire Grounding, Non-Nema, Screw Terminal, Steel |
| Weight per unit  | 0.8500 (lbs/each)  |
| Product Category | Plugs, Connectors, Inlets, Out   |

### Features

|                     |                           |
|---------------------|---------------------------|
| amperage rating     | 50                        |
| connection          | Pressure Screw Terminals  |
| Current Rating      | 50                        |
| Dielectric Strength | Withstands 2,000V minimum |
| Number of Wires     | 4-Wire                    |
| pallet quantity     | 810                       |
| Phase               | 1                         |
| Poles               | 3-Pole                    |
| Voltage Rating      | 125/250 VAC               |
| Wattage             | 12,500                    |
| Wire Size           | #10 to #6                 |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | 2.17 in x 3.50 in x 2.62 in |
|------|-----------------------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | LKG INLT, 50A 125/250V, 3P4W  |
| extra long description | HWDK CS6375 LKG INLT, 50A 125/250V,   |
| Features               | Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief. |
| Long Description       | Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel  |
| Product Type           | LKG Inlt, 50A 125/250V, 3P4W  |
| Special Features       | Standard Product  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585828206        |
| Manufacturers Part Number | CS6375                |
| UPC                       | 783585828206          |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type                 | Flanged Inlet                                       |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.85 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Extra Heavy Duty Industrial                     |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting                 | Screw Mount                                     |
| nema rating              | Non-NEMA  |
| standard                 | Certified to CSA C22.2 No.42;Listed to UL 498   |