

# Eaton CRC6034BC

Catalog Number: CRC6034BC

Eaton Crouse-Hinds series PowerMate CRC connector, 60A, 0.440-1.375", Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



| Product Name                                      | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series PowerMate CRC connector | CRC6034BC      |
|   | UPC            |
|   | 662276276598   |
| Product Length/Depth                              | Product Height |
| 8.3 in  | 2.31 in        |
| Product Width                                     | Product Weight |
| 2.31 in   | 2.2 lb         |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

60A

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

0.440-1.375"

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds CRC6034BC 3D drawing](#)

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

### Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

### Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CRC6034BC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CRC6034BC

Catalog Number: CRC6034BC

Eaton Crouse-Hinds series PowerMate CRC connector, 60A, 0.440-1.375", Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



| Product Name                                      | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series PowerMate CRC connector | CRC6034BC      |
|   | UPC            |
|   | 662276276598   |
| Product Length/Depth                              | Product Height |
| 8.3 in  | 2.31 in        |
| Product Width                                     | Product Weight |
| 2.31 in   | 2.2 lb         |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

60A

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

0.440-1.375"

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds CRC6034BC 3D drawing](#)

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

### Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

### Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CRC6034BC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)