



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS8269 Locking RCPT 50A 250V, 2P3W *Hubbell Wiring Devices*

Catalog Number	CS8269
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A, 250V, 2-Pole 3-Wire Grounding, Non-Nema, Screw Terminal, Black
Weight per unit	0.2150 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	50
connection	Screw Terminal
Current Rating	50
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	1600
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	12,500
Wire Size	#10 to #6

### Dimensions and Weight

Size	2.69 in x 2.12 in x 2.36 in
------	-----------------------------

### Descriptions

Description	LOCKING RCPT 50A 250V, 2P3W
extra long description	HWDK CS8269 LOCKING RCPT 50A 250V,
Features	Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief.
Long Description	Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A, 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black
Product Type	Locking RCPT 50A 250V, 2P3W
Special Features	Standard Product



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585828909
Manufacturers Part Number	CS8269
UPC	783585828909

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE

## Packaging

Carton	1
Package	10
Weight Per each	0.215

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	Non-NEMA
standard	Certified to CSA C22.2 No.42;Listed to UL 498