



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB20AC3GRY 20A 120/277VAC B+S Wire Comm 3W SW Gy

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | CSB20AC3GRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Construction 3WAY Switch, Back and, Side Wire, 20AMP 120/277VOLT, Gray. |
| Weight per unit | 0.1893 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------------|--|
| amperage rating | 20 |
| connection | Side Wire or external screw-pressure plate |
| Connection Type | Wired |
| Contact Configuration | One piece brass alloy contact arm |
| Contact Rating | Oversized silver alloy contacts |
| Degree of Protection | 1500V Dielectric Withstand Voltage |
| indoor/outdoor | Indoor |
| insulation | False |
| Material | Thermoplastic |
| Poles | 3-way |
| Switch Type | Toggle |
| Voltage | 120/277 V |
| Voltage Rating | 120/277 |
| Wattage | 3 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 20A 120/277VAC B+S WIRE COMM 3W SW GY |
| extra long description | P&S CSB20AC3GRY 20A 120/277VAC B+S |
| Long Description | Construction 3way Switch, Back and, Side Wire, 20amp 120/277volt, Gray. |
| Product Type | 20A 120/277VAC B+S Wire Comm 3W SW Gry |
| Special Features | Back & Side wire, locking support, one piece brass alloy contact arm |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007126266 |
| Manufacturers Part Number | CSB20AC3-GRY |
| UPC | 785007126266 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.1893 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Commercial |
| Mounting | WALL |
| nema rating | WD-1 and WD-6 |
| standard | CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2 |