



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



CSB115LA Switch Toggle SP 15A 120/277V B/Swire La *Eaton Wiring Devices*

Catalog Number	CSB115LA
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Toggle Switch, #14-10 Awg, 15A, Flush, 120/277V, Back and Side, Screw, Light Almond, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	15
dimensions	1.3000 IN X 0.9020 IN X 4.2000 IN
Material	PVC
Poles	1
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOGGLE SP 15A 120/277V B/SWIRE LA
extra long description	EWD CSB115LA Switch Toggle SP 15A 1
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade toggle switch, #14-10 AWG, 15A, Flush, 120/277V, Back and side, Screw, Light almond, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Product Type	Switch Toggle SP 15A 120/277V B/Swire La
Special Features	Commercial Grade

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664719028
Manufacturers Part Number	CSB115LA
UPC	032664719028

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade toggle switch

Packaging

Carton	1
Package	50
Weight Per each	0.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

cULus Listed,Federal Specification Classification 6241 05,NOM