



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CTRP253PWH Contour 250W Led/Electronic Low Voltage White

Lutron

Catalog Number	CTRP253PWH
Manufacturer	Lutron
Description	Skylark Contour Reverse-Phase Dimmer With On/Off Switch, CFL/Led (Screw-Based), Incandescent/Halogen, Electronic Low-Voltage, 3-Way/Single-Pole, 250W CFL/Led or 500W Inc/Hal/Elv In White
Weight per unit	0.3800 (lbs/each)
Product Category	Lighting Dimmers

### Features

Connection Type	Wire Leads
insulation	Plastic
Poles	1
Switch Type	Paddle Switch
Voltage Rating	120
Wattage	250/500

### Material, Color, and Finish

Finish	Gloss
--------	-------

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	CONTOUR 250W LED/ELECTRONIC LOW VOLTAGE WHITE
extra long description	LUT CTRP-253P-WH SKYLARK CONTOUR 25
Long Description	Skylark Contour Reverse-phase Dimmer with on/off switch, CFL/LED (Screw-based), Incandescent/Halogen, Electronic Low-voltage, 3-way/single-pole, 250W CFL/LED or 500W inc/hal/ELV in white
Product Type	Skylark Contour 250W Led In White
Special Features	Controls 120 V/250 W LED/CFL, and 500 W Inc and ELV loads. Paddle turns on/off. Slide up to brighten, down to dim.

### Manufacturer Information

Brand	Lutron
GTIN	00784276226417
Manufacturers Part Number	CTRP-253P-WH
UPC	784276226417

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, reverse-phase, 3-way/single-pole



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.38

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
standard	UL, CSA, NOM