



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D5057 Classic Klaw Pump Pliers, 7" *Klein Tools*

| | |
|------------------|-------------------------------------|
| Catalog Number | D5057 |
| Manufacturer | Klein Tools |
| Description | Klein D5057 Classic Klaw™ Pump Plie |
| Weight per unit | 0.4100 (lbs/each) |
| Product Category | 20240712100444 |

Features

| | |
|----------------|--------------------------|
| Handle Length | 6" (15.2 cm) |
| Handle Type | Forged |
| Jaw Length | 0.85" (2.2 cm) |
| Jaw Width | 0.25" (0.6 cm) |
| Material | Induction Hardened Steel |
| Overall Height | 7" (17.8 cm) |
| Overall Width | 0.48" (1.2 cm) |
| tether capable | No |

Material, Color, and Finish

| | |
|-----------------|--------|
| Handle Color | Yellow |
| Handle Material | Steel |

Dimensions and Weight

| | |
|----------------|----------------|
| Overall Length | 1.38" (3.5 cm) |
|----------------|----------------|

Descriptions

| | |
|------------------|-------------------------------------|
| Description | CLASSIC KLAW PUMP PLIERS, 7" |
| Long Description | KLEIN D5057 Classic Klaw™ Pump Plie |
| Product Type | Classic Klaw™ Pump Pliers, 7" |
| Special Features | Curved Jaw; Hardened Teeth |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Klein Tools |
| GTIN | 00092644730351 |
| Manufacturers Part Number | D5057 |
| UPC | 092644730351 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | Pliers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----------------|
| Carton | 1 |
| Package | 6 |
| Weight | 6.3 oz (0.2 g) |
| Weight Per each | 0.41 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------|
| Application | General Purpose |
| standard | — |