



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D2488INS Diagonal Cutting Pliers, Insulated, High-Leverage, *Klein Tools*

Catalog Number	D2488INS
Manufacturer	Klein Tools
Description	These Insulated Diagonal-Cutting Pliers Feature Two Layers Of Insulation to Protect Against Electric Shock. Clearly Marked With The Official 1000V Symbol, These Pliers Meet or Exceed Astm F1505-16 and IEC 60900:2018 Standards For Insulated Tools. The Head Is Angled to Get Into Confined Spaces. The High-Leverage Design Provides 36-Percent Greater Cutting Power Than Other Plier Designs.
Weight per unit	0.7000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Length	4.9" (12.4 cm)
Jaw Length	0.813" (2.1 cm)
jaw thickness	0.46" (1.2 cm)
Jaw Width	1.25" (3.2 cm)
Material	Induction Hardened Steel
media	Yes

Material, Color, and Finish

Handle Color	ORANGE
--------------	--------

Dimensions and Weight

Overall Length	8.24" (20.9 cm)
----------------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DIAGONAL CUTTING PLIERS, INSULATED, HIGH-LEVERAGE,
extra long description	KLEIN D248-8-INS 8" Diagonal Cuttin
Features	These Insulated Diagonal-Cutting pliers feature two layers of insulation to protect against electric shock. Clearly marked with the official 1000V symbol, these pliers meet or exceed ASTM F1505-16 and IEC 60900:2018 standards for insulated tools. The head is angled to get into confined spaces. The high-leverage design provides 36-percent greater cutting power than other plier designs.
Long Description	These Insulated Diagonal-Cutting pliers feature two layers of insulation to protect against electric shock. Clearly marked with the official 1000V symbol, these pliers meet or exceed ASTM F1505-16 and IEC 60900:2018 standards for insulated tools. The head is angled to get into confined spaces. The high-leverage design provides 36-percent greater cutting power than other plier designs.
Product Type	8" Diagonal Cutting Pliers Angled
Special Features	Flame Retardant and Impact Resistant Handle

Manufacturer Information

Brand	Klein Tools
GTIN	00092644720710
Manufacturers Part Number	D2488INS
UPC	092644720710

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Diagonal Cutting Pliers

Packaging

Carton	1
Package	3
Weight	11.2 oz (318 g)
Weight Per each	0.7

Uses, Certifications, and Standards

Application	ACSR, Screws, Nails and Most Hardened Wire
Configuration	Angled Nose
standard	IEC 60900 and ASTM F1505