



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DC132030NBA20CE1 DC1 IP20 240V 3PH In/3PH Out 10HP 30A Enh FW Eaton Corp

Catalog Number	DC132030NBA20CE1
Manufacturer	Eaton Corp
Description	Eaton Powerxl DC1 Series Adjustable Frequency Drives, IP20 240V 3PH In/3PH Out 10HP, 30A Enh FW
Weight per unit	16.0 (lbs/each)
Product Category	Ac Drives

### Features

dimensions	22.1000 IN X 11.4000 IN X 13.3000 IN
------------	--------------------------------------

### Descriptions

Description	DC1 IP20 240V 3PH IN/3PH OUT 10HP 30A ENH FW
extra long description	ETN DC1-32030NB-A20CE1 PowerXL DC1
Features	The PowerXL DC1 compact variable frequency drive stands out with its small size and user-friendly interface. The DC1 was specifically developed for use in standard applications such as fans, pumps and conveyors. With the activation of additional parameters and functionalities, the DC1 can also cover demanding applications involving IE4 (Super Premium Efficiency) motors. Thanks to their quick and simple commissioning, the DC1 drives are ideally suited for serial production.
Long Description	Eaton PowerXL DC1 series Adjustable Frequency Drives, IP20 240V 3PH IN/3PH OUT 10HP, 30A ENH FW
Product Type	Powerxl DC1 Adjustable Frequency Drives

### Manufacturer Information

Brand	Eaton
GTIN	00786687020011
Manufacturers Part Number	DC1-32030NB-A20CE1
UPC	786687020011

### Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Adjustable frequency drive

### Packaging

Carton	1
Weight Per each	16



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMsElec Assemblies, Panels & OEM - Electrical  
Assemblies and OEMs - Other

standard

UkrSepro,EN 60529,cUL Certified,UL Listed,EN 61800-3,EN  
61800-5-1