



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH221FGK 30A/2P HD Fusible Safety Switch 240V Nema 1

Eaton Corp

Catalog Number	DH221FGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, Enhanced Visible Blade, 30 A, Nema 1, Painted Steel, Class H, Fusible Without Neutral, Two-Pole, Two-Wire, 240 V, Max HP: 1.5, 5 HP (1PH @240V/250 VDC), #14-#2 Cu/Al
Weight per unit	14.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	30
dimensions	18.0000 IN X 9.5000 IN X 7.5000 IN
Material	Painted Steel
media	Yes
Poles	2
Voltage Rating	240V

Dimensions and Weight

Depth	18
Height	7.5
Width	9.5

Descriptions

Description	30A/2P HD FUSIBLE SAFETY SWITCH 240V NEMA 1
extra long description	ETN DH221FGK 30A/2P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 30 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Two-pole, Two-wire, 240 V, Max Hp: 1.5, 5 hp (1PH @240V/250 Vdc), #14-#2 Cu/Al
Product Type	30A/2P HD Fusible Sfty SW 240V N1
Special Features	Enhanced visible blade

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114370322
Manufacturers Part Number	DH221FGK
UPC	782114370322



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 14

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 1

standard UL Listed, NEC 230.62 (C) Compliant Barrier